
Ralpa

Orbital shaker "ORBI-300"



ORBI-300 + PL-UN-300

Features

- Speed regulation by microprocessor. LCD display.
- Max. Speed of 300 r.p.m.
- Programmable delayed start between 0 and 99 h
- Progressive start and stop.
- Orbit width: 20 mm.
- Max. load : 15 kg.
- Programmable shaking time (0-99 hours).
- Acoustic alarm at the end of process
- Overload safety system
- External metallic case oven painted with epoxy resin.
- Several compatible platforms for different applications

R. Espinar, S.L. <u>www.raypa.com</u> Tel.: +34 93 783 0720



Orbital shaker "ORBI-300"

Reference	Max. Speed	Dimensions platform	H x A x F ext. en mm	Power W	Weight kg./
ORBI-300	30- 300 rpm	420 x 300 mm	155 x 460 x 370	40	7

ACCESSORIES

Multi purpose tray (420 x 300 mm.)

Reference: PL-UN-300



Reference: PL-RO

Reference: PL-AD-300

Anti-slipping tray (420 x 350 mm.)




Tray with adhesive mat (420 x 300 mm.)


Designed to secure any flat-bottomed glass-ware or plastic-ware: micro or deep well plates, Erlenmeyer or Fernbach flasks, round or square bottles...

Speeds of up to 250 rpm depending only on the shape and weight of the container and the shaking orbital diameter. Easy to clean.

Reference: PL-ADH-300











R. Espinar, S.L. <u>www.raypa.com</u> Tel.: +34 93 783 0720